





Recessed Dialysis Supply & Waste Box

Provides a recessed connection and drain for operation of Dialysis machines available with stainless steel or PVC valves.

From the original, Guy Gray heavy-duty brand of Recessed Outlet Boxes comes the new line of Dialysis Boxes. This series of boxes, when supplied with valves, is designed specifically for reverse osmosis and deionized water mixed with dialysate saline concentrate. These sturdy boxes are built from 316 stainless steel preventing corrosion, are available with stainless steel or PVC valves, and contain a 2" waste outlet. Available configurations include: no valves, one valve or two supply valves, with and without a locking door. Two adjustable, stainless steel mounting flanges are supplied for easy securement of box to wall and eliminates the need to build supports.







RECESSED DIALYSIS SUPPY & WASTE BOX





PRODUCT FEATURES

HIGHLIGHTS

- Access door and frame may be positioned in any convenient orientation; allows door to open from top, bottom, left or right.
- Door includes concealed hinge with Cam Cylinder Lock and two keys.
- Equipment drain tube support is located directly over the drain to eliminate splatter and minimize clean-up
- Available with stainless steel or PVC valves, in no valve, one valve, or two valves for custom configuration

- · Interior seams are continuous welded to provide a water-tight seal
- Adjustable stainless steel frame provides a clean finish. Frame can accommodate up to two 5/8" drywall; secure with Phillips head screws (supplied)
- Waste outlet can be directly connected to 2" nominal size glass or plastic drain with mechanical coupling
- Two adjustable stainless steel mounting flanges provide easy securement of box to wall, eliminating the need to build supports
- PVC valves are ball type with EPDM seals and 0-ring; ½" FPT Schedule 80; flushing nipple included
- Tapped holes on mounting plate allow for easy assembly of valves

PRODUCT	DESCRIPTION	MODEL	UPC	CUBIC FT./CASE	UNITS/CASE	LBS/CASE
PVC Valves	S			•		
82643	One Valve, Less Door	DBSS1	012181-826430	1.05	4	26
82644	One Valve, Locking Door	DBSS1D	012181-826447	1.05	4	28
82645	Two Valves, Less Door	DBSS2	012181-826454	1.05	4	26
82646	Two Valves, Locking Door	DBSS2D	012181-826461	1.05	4	28
82647	One Valve Hole, Less Valves, Locking Door	DBSS1DLV	012181-826478	1.05	4	28
82648	Two Valve Holes, Less Valves, Locking Door	DBSS2DLV	012181-826485	1.05	4	28
Stainless	Steel Valves					
82688	One Valve, Less Door	DBSS1SV	012181-826881	1.05	4	22
82689	One Valve, Locking Door	DBSS1DSV	012181-826898	1.05	4	27
82690	Two Valves, Less Door	DBSS2SV	012181-826904	1.05	4	26
82691	Two Valves, Locking Door	DBSS2DSV	012181-826911	1.05	4	31

To change door orientation, rotate and secure frame to box and then latch door in place.

