


# DU•ALL™ Dual Drain Washing Machine Outlet Box

FEATURING EZ•OUT™ TEST CAP



## STANDARD WASHER BOX FEATURES:

- Our one piece design speeds installation vs separate drain and valve boxes
- Depth of the box rests against the back sheetrock wall for sturdy installation
- Side of the box has a flat side for secure mounting to wall
- The frame is interchangeable with center drain washing machine outlet boxes

## KEY DUAL DRAIN FEATURES:

- 1 Solid one piece construction with raised drip guard contains and sends valve or washing machine hose leaks down the drain
- 2 Forward mounted valves give easy access to homeowners for on/off operation
- 3 Drains positioned toward back of box for connection to trap from either side

## DU•ALL DUAL DRAIN FEATURES:

- 4 Various valve mounting options allows dual drain, right drain only or left drain only
- 5 Box can be inverted for top mount valves/center drain option
- 6 EZ Out Test caps are raised for EZ removal and KO's are oversized so they won't fall down the drain

# Flexible Valve Mounting Options




Left Mount Valves, Right Drain



Center Mount Valves, Left or Right Drain



Right mount Valves, Left Drain



Valves Forward w/ Auxiliary Drain Line & Washer Discharge Line



Left Top Mount Valves, Center Drain



Center Top mount Valves, Center Drain




Right Top Mount Valves, Center Drain




Valves Forward with Studor AAV & Washer Discharge Line


## EZ•OUT™ TEST CAP ARE RAISED UP FOR EZ REMOVAL




1 Position flathead screwdriver at intersection of bottom wall and raised test cap.



2 Hit screwdriver until it penetrates under test cap.



3 Rotate screwdriver lifting up test cap.



4 Reach in with hand or pliers and remove test cap.

## VALVE CONNECTIONS



1/2" COPPER SWEAT



1/2" CPVC ASTM D2846



1/2" CRIMP ASTM F1807



1/2" COLD EXPANSION ASTM F1960



LONG SHANK EXTENTION



REAHU EVERLOC+™



F3347



500 Distribution Parkway, Collierville, TN 38017 • Phone: 800-888-8312 • Fax: 901-853-5008 • ipscorp.com